
# Fan-Coils, VAV Boxes, Blower-Coils, and Air Handlers

# **FAN-COIL UNITS**

HLF Horizontal, Low-Profile, Free-Return 200-1200 CFM





HLP Horizontal, Low-Profile, Plenum-Return 200-1200 CFM

HLE Horizontal, Low-Profile, Exposed-Cabinet 200-1200 CFM





HPF Horizontal, High-Performance, Free-Return 600-2400 CFM

HPP Horizontal, High-Performance, Plenum-Return 600-2400 CFM





HPE Horizontal, High-Performance, Exposed-Cabinet 600-2000 CFM



CDV Vertical, High-Performance 400-2000 CFM







VHA/VHB Vertical, Hi-Rise, Tandem Units 350-1200 CFM







VFE Vertical, Floor, Exposed-Cabinet 250-1200 CFM

VFS Vertical, Floor, Slope-Top 250-1200 CFM





VFC Vertical, Floor, Wall-Mount, Concealed 250-1200 CFM

VLE Low-Height, Vertical, Wall-Mount, Exposed 200-600 CFM





VLC Low-Height, Vertical, Wall-Mount, Concealed 200-600 CFM



# Fan-Coils, VAV Boxes, Blower-Coils, and Air Handlers

#### **BLOWER-COIL UNITS**



HDD Horizontal, Direct-Drive 250-5000 CFM







VB Vertical, Bottom-Return, Reduced-Footprint, Belt-Drive, 800-3000 CFM



# **AIR-HANDLING UNITS**

MQL Modular Indoor Air Handler 1000-8500 CFM



# **VAV TERMINAL UNITS**



SDR Single-Duct 100-8000 CFM







SGX Retrofit Unit Supply & Exhaust 50-4000 CFM

DDR Dual Duct 100-4000 CFM





CRB Series-Flow, Constant-Volume, Fan-Powered 100-4400 CFM



CRQ Series-Flow, Constant-Volume, Fan-Powered, Ultra-Quiet 100-4400 CFM

CRC Series-Flow, Constant-Volume, Fan-Powered, Sensible Cooling 100-2000 CFM





CFR Series-Flow, Constant-Volume, Fan-Powered 100-4800 CFM

CFRQ Series-Flow, Constant-Volume, Fan-Powered, Extra-Quiet 200-3100 CFM





CFL Series-Flow, Fan-Powered Low-Height 100-1900 CFM

VFR Parallel-Flow, Variable-Volume, Fan-Powered 100-4100 CFM





VFL Parallel-Flow, Fan-Powered Low-Height 100-3000 CFM

