# VB/VR Blower-Coil Units Reduced-Footprint, Vertical





# Models VB/VR: Big on Features, Small in Size

#### Contractors

All VB/VR model blower-coil units are shipped completely assembled, reducing field-installation time and labor. All units are thoroughly inspected and tested prior to shipment, eliminating potential problems at startup. Motor wiring is brought to a junction box and terminated. The junction box is located on the outside of the unit casing, reducing electrical hook-up time.




A wide variety of fan-discharge configurations allow for increased flexibility and easier installation on the jobsite, resulting in cost reductions by eliminating expensive elbows, etc.

#### Designers

The extensive variety of standard options available on the VB/VR units are where you find the versatility to fit any HVAC system designer's needs.

Options include: Mixing boxes with standard low-leak dampers, blow-thru electric heat with single-point power connection. All electric heat units are listed with ETL as an assembly and carry the cETL label.

#### **Typical Installations**



Model VR, Rear Return with Mixing Box Mechanical Room Layout


High-efficiency motors, starters, disconnects, fusing, and piping packages mean easier coordination between mechanical and electrical trades. Coil options allow for 4 or 6-row cooling coils.

#### **Owners**

VB/VR model blower coils are constructed from galvanized steel, surpassing the ASTM 125-hour, salt-spray test for corrosion and rust. Insulation, which is 1-inch thick, scrimreinforced, and foil-faced, is glued, pinned and taped for maximum adhesion. Insulation complies with UL 181, ASTM-C1071, NFPA 90A and 90B and meets bacteriological standard ASTM-C665 and C1136 for mold, mildew and humidity resistance.


All units, with or without electric heat, are cETL-listed and labeled. All wiring is in compliance with NEC, assuring safety and quality for the owner.







Model VB, Bottom Return with Return Plenum Closet or Confined Space Layout

### VB/VR Unit Dimensions, Coil and Filter Data







#### **DIMENSIONS** - In [mm]

UNIT SIZE	н	w	L	A	В	с	D
08	46	26	19	6-1/2	6-7/8	9-9/16	16
	[1168]	[660]	[483]	[165]	[175]	[243]	[406]
12	46	26	21	7-1/2	8-1/4	8-7/8	20
	[1168]	[660]	[533]	[190]	[210]	[225]	[508]
16	54	29	25	7-1/2	10-1/4	9-3/8	24
	[1372]	[737]	[635]	[190]	[260]	[238]	[610]
20	54	29	28	11-3/8	13–1/4	7-7/8	24
	[1372]	[737]	[711]	[289]	[337]	[200]	[610]
25	60	39	28	16	12-7/8	13-1/16	24
	[1524]	[991]	[711]	[406]	[327]	[332]	[610]
30	60	39	28	16	15	12	24
	[1524]	[991]	[711]	[406]	[381]	[305]	[610]

#### Coil Face Area and Filter Data


Unit Size	Nominal CFM	Internal Cooling And Heating Coils	Discharge Section Heating Coils	2" Filters (Quantity) And Size		Filter Face Area
08	800	2.1 [0.20]	2.1 [0.20]	(1) 16" x 20" x 2"	[406 x 508 x 51]	2.2 [0.20]
12	1200	2.8 [0.26]	2.1 [0.20]	(1) 20" x 20" x 2"	[508 x 508 x 51]	2.8 [0.26]
16	1600	3.6 [0.33]	3.2 [0.30]	(1) 24" x 24" x 2"	[610 x 610 x 51]	4.0 [0.37]
20	2000	4.8 [0.45]	3.2 [0.30]	(1) 24" x 24" x 2"	[610 x 610 x 51]	4.0 [0.37]
25	2500	5.7 [0.53]	4.6 [0.43]	(1) 24" x 24" x 2" (1) 12" x 24" x 2"	[610 x 610 x 51] [305 x 610 x 51]	6.0 [0.56]
30	3000	6.8 [0.63]	5.7 [0.53]	(1) 24" x 24" x 2" (1) 12" x 24" x 2"	[610 x 610 x 51] [305 x 610 x 51]	6.0 [0.56]

#### NOTES:

1. Standard filters are 2" throwaway; optional filters are 2" pleated.

2. Filter sizes are nominal and standard size, measured in inches [mm].

3. Coil and filter face areas are measured in square feet [square meters].



#### NOTES:

- 1. All dimensions are inches [mm] and are +/- 1/4" [6mm]. Metric values are soft conversions.
- 2. Motor/drive location may be specified Left or Right Hand. Standard control-enclosure location matches motor/drive position.
- 3. Provide sufficient clearance to access electrical controls and comply with all applicable codes and ordinances.
- 4. Maximum total internal coil rows: 6.
- 5. Left-hand unit shown; right-hand unit has CW and HW piping connections mirrored.
- 6. Filter assembly runs the full length of the unit size.
- 7. Drawings not for installation purposes.

**Note:** Drawings are not to scale and are not for installation purposes. Refer to www.enviro-tec.com for current submittal drawings. All data and dimensions are subject to change without notice.

## **VB/VR Blower-Coil Unit Features**

#### **STANDARD FEATURES:**

#### Construction

- Galvanized-steel cabinet construction, minimum 18 gauge
- 1"-thick, 1.6-lb/ft<sup>3</sup> scrim-reinforced, foil-faced insulation, glued, taped and pinned in place
- 1" supply duct collars
- Gasketed, removable access panel sized for easy handling
- Galvanized-steel drain pan with 1-1/8" ODM copper pipe outlet
- · Left- and right-hand arrangement

#### Fan Assembly

- · Forward-curved (double-width, double-inlet) fans
- Statically and dynamically balanced
- Solid steel shafting
- $\cdot$  Ball bearings with a minimum design-average life (L  $_{\rm 50}$  ) of 100,000 hours

#### Fan Motor and Drive

- NEMA-design ODP motors
- 1750 RPM, single-speed, 60 Hertz
- · Single-phase motors with inherent thermal protection
- Three-phase motors
- · Rigid-mount, adjustable, motor base
- Standard cross-section "V-belt" drive with 1.2 service factor
- Adjustable-pitch motor pulley and fixed-pitch blower pulley

#### Coils

- · AHRI Standard 410-certified and labeled
- 1/2" O.D. seamless copper tubes
- Collared and corrugated aluminum fins
- Manual air-vent plug on all water coils
- 450 PSIG working pressure at 200°F
- Steam coils rated at 15 PSIG maximum
- $\cdot$  Copper sweat connections
- · 0.016" tube wall on water and evaporator coils
- · 0.025" tube wall on steam coils
- High-efficiency, aluminum-fin surface for optimizing heat transfer, pressure drop, and carryover

#### **Filters and Filter Rack**

- Top-access, flat-filter rack (VR only)
- Front-access filter rack (VB only)
- · Standard-size, 2" nominal, throwaway filters

#### **Electrical**

- Fan motor wired and terminated to J-box
- All units ETL-listed in compliance with UL/ANSI Standard 1995

#### **OPTIONAL FEATURES:**

#### Construction

- Stainless-steel drain pan with 1" MPT galvanized pipe outlet
- External rubber-in-shear or spring-type vibration isolators, floor mount
- Fan-discharge arrangements
- Discharge plenum w/dbl.-deflection discharge grille
- Access panel with lift-and-turn fasteners
- Double wall access panel w/lift-and-turn fasteners
- Return plenum with removable panels (VB only)
- Base rails with rigging slots, factory-assembled and installed

#### Fan Motor and Drive

#### TEFC motors

High-efficiency motors

#### Coils

- 4 and 6-row chilled-water or R-22 DX coils
- · 1 and 2-row hot-water coils
- 1 and 2-row hot-water or standard-steam coils
- in discharge-coil section only • Hot-water coil in preheat or reheat position
- Stainless-steel coil casings
- 0.025" tube wall on water and evaporator coils
- Auto air vents on water coils

#### Piping Packages

- $\cdot$  1/2", 3/4", 1", 1¼", 1½" 2-way and 3-way, normally closed, two position electric motorized valves
- · Isolation ball valves with memory stop
- 24V floating point modulating control valves
- 0-10V proportional control valves
- Fixed (FC) and adjustable (PICV) flow control devices

### Y-strainers, P/T ports

#### Filters and Filter Rack

- Side-access filter rack (VR only)
- 2" pleated filter (MERV 6)
- Spare throwaway or pleated filters

#### Inlet-Damper Section (VR rear-return unit)

- · Factory-assembled and installed
- · Heavy-gauge, galvanized-steel, formed blade dampers
- $\cdot$  Low-leak dampers with extruded-vinyl blade seals
- and flexible-metal jamb seals
- Parallel-blade operation
- Interconnecting damper linkage

#### Electrical

- Motor wiring in conduit
- Motor starter (contactor with overload for three-phase; contactor for single-phase), factory-installed (mounted and wired)
- Door-interlocking disconnect switch (non-fused) (with main fusing)
- · Hand-off-auto switch (HOA)
- Main fusing

#### **Electric Heat Section**

• Factory-mounted electric heater with single-point power connection, ETL-listed as an assembly

ENVIRO-TEC is a registered trademark of Johnson Controls, Inc. in the United States of America and other countries. Other trademarks used herein may be trademarks or registered trademarks of other companies.

