

CSC-2000 SERIES Reset Volume Controllers

DESCRIPTION

The CSC-2000 series are designed for use on VAV terminal units in HVAC systems.

These are submaster air velocity controllers whose velocity setpoint is reset between adjustable minimum and maximum limits by a master controller, typically a room thermostat.

Available as direct acting for normally open VAV terminal units, and reverse acting for normal closed VAV terminal units.

Each is equipped with separate adjustment knobs for minimum and maximum airflow settings. CSC-2001 and 2002 hare equipped with 0 to 10 reference dials, while all others have blind adjustments. All models should be calibrated with the use of airflow measuring equipment.



MODELS

| Model | Thermostat Required: | | Setpoint Range | | Reset Pressure | Air Consumption |
|----------------------|----------------------|-------------|---|--------------------------|---------------------|---|
| | For Cooling | For Heating | Minimum | Maximum | Band | Air Consumption |
| CSC-2001 CSC-2003 | DA | RA | 0-1.0° wg (249 Pa) | Min. plus 1" wg (249 Pa) | 8 (±0.5) to 13 psig | 14.4 scim |
| CSC-2007 | | | | | | 11.5 scim @ 20 psig (3.1 mL/s @ 138 kPa) |
| CSC-2009 | | | 0-2.0" wg (498 Pa) | Min. plus 2* wg (498 Pa) | | |
| CSC-2011 | | | Same as CSC-2001 without mounting bracket | | (55 ±0.3 to 90 kPa) | 14.4 scim @ 20 psig (3.9 mL/s @ 138 kPa) |
| CSC-2013 | | | Same as CSC-2003 without mounting bracket | | | |
| CSC-2015 | | | Same as CSC-2009 without mounting bracket | | | |
| CSC-2017 | | | 0-2.0* wg (498 Pa) | Min. plus 2" wg (498 Pa) | | 11.5 scim @ 20 psig (3.1 mL/s @ 138 kPa) |
| | | | or Normally-Closed Dan | npers (Gray Controllers) | | |
| CSC-2002 CSC-2004 | | DA | 0-1.0" wg (249 Pa) | Min. plus 1" wg (249 Pa) | 3 (±0.5) to 8 psig | 14.4 scim @ 20 psig (3.9 mL/s @ 138 kPa) |
| CSC-2008 | RA | | | | | 11.5 scim @ 20 psig (3.1 mL/s @ 138 kPa) |
| CSC-2010 | | | 0-2.0" wg (498 Pa) | Min. plus 2" wg (498 Pa) | | |
| CSC-2012 | | | Same as CSC-2002 without mounting bracket | | (21 ±0.3 to 55 kPa) | 14.4 scim @ 20 psig |
| CSC-2014 | | | Same as CSC-2004 without mounting bracket | | | (3.9 mL/s @ 138 kPa) |
| CSC-2016 | | | Same as CSC-2010 without mounting bracket | | | |
| CSC-2018 | | | 0-2.0° wg (498 Pa) | Min. plus 2" wg (498 Pa) | | 11.5 scim @ 20 psig (3.1 mL/s @ 138 kPa |

SPECIFICATIONS

| Output Sensitivity | 3 psig/.01" wg (21 kPa/ 2 Pa) | | |
|---|--------------------------------|--|--|
| Air | o polgrior wg (21 Ki ur 21 ur | | |
| 1 | 45 (2.00 22) (400 (2.007 1.02) | | |
| Main Pressure | 15 to 30 psig (103 to 207 kPa) | | |
| Maximum Signal Pressure | | | |
| 6" wg (1493 Pa) applied to either port (X or Y) | | | |
| Ambient Limits | | | |
| Operating | 40°F to 120°F (4°C to 49°C) | | |
| Shipping | -40°F to 140°F (-40°C to 60°C) | | |
| Material | ABS (Beige or gray) | | |
| | UL Flame Class 94HB | | |
| Weight | 7.5 oz (213 grams) | | |

ORDERING


Specify: Model Number


Order From: Local KMC Controls representative or,


KMC Controls, Kreuter Manufacturing Co., Inc.


DIMENSIONS IN INCHES (MM)

| PORTS | DIAMETER | TUBING "FR" SIZE |
|-------|------------|---------------------|
| Х | 1/4" O.D. | 3/8" O.D. |
| Υ | 1/4" O.D. | 3/8" O.D. |
| М | 3/16" O.D. | 1/4" O.D. |
| В | 3/16" O.D. | 1/4" O.D. |
| Т | 3/16" O.D. | 1/4" O.D. |









INSTALLATION-CALIBRATION

The series of reset volume controllers may be mounted in either a horizontal or vertical plane. Other angular positions are not recommended. They should be calibrated in the same plane as they will be mounted.

For Beige Units: Normally open damper with direct acting thermostat for cooling or reverse acting thermostat for heating.

- Connect total pressure to "X" and static pressure to "Y".
- 2. Adjust "LO" center knob to desired airflow with 0 psi at "T" port.
- 3. Adjust "HI" outer knob to desired airflow with 15 psi at "T" port.

For Gray Units: Normally closed damper with reverse acting thermostat for cooling, or direct thermostat for heating.

- 1. Connect total pressure to "Y" and static pressure to "X".
- 2. Adjust "HI" center knob to desired airflow with 0 psi at "T" psi.
- 3. Adjust "LO" outer knob to desired airflow with 15 psi at "T" port.

These devices should be supplied with clean, dry control air only. No attempt should be made to use any other medium.

MAINTENANCE

No routine maintenance is required. Each component's design and material selection assures dependable long-term reliability and performance.

Careful installation will also enhance long-term reliability and performance.



Revised 1/10/97

TECHNICAL BULLETIN

CSC-2000 SERIES RESET VOLUME CONTROLLER [Gray]

DESCRIPTION


These controllers are for use on Normally Closed dampers. These are differential pressure (ΔP) sub-master controllers reset by a master controller. The master controller is typically a room thermostat. These controllers have a reset range of 3 to 8 psig. The spring range of the actuator does not matter to the controller, however sufficient main air is required to provide the actuator with enough force to operate the damper/linkage. Any sequencing with other controllers, valves or pneumatic-electric relays must be sequenced with the controller's reset range, NOT the actuator's range. These controllers are typically used on single duct applications, and may be found in dual duct applications. When working on dual duct applications it may be necessary to work on one duct at a time while closing off the other.

| Controller Color | Gray | |
|-------------------------|------------------------------------|--|
| Controller Reset Action | Reverse Acting | |
| Controller Action | Reverse Acting | |
| LO Limit (Minimum) | > 8 psig | |
| HI Limit (Maximum) | < 3 psig | |
| Cooling Application | Reverse Acting Thermostat Required | |
| Heating Application | Direct Acting Thermostat Required | |

AVAILABLE MODELS

- 1. CSC-2002; 0 to 1" ΔP , 14.4 scim air consumption, with 0 to 10 reference dial.
- 2. CSC-2004; 0 to 1" Δ P, 14.4 scim air consumption.
- 3. CSC-2008; 0 to 1" ΔP , 11.5 scim air consumption.
- 4. CSC-2010; 0 to 2" ΔP , 14.4 scim air consumption.
- 5. CSC-2012; same as CSC-2002 supplied less a mounting bracket.
- 6. CSC-2014; same as CSC-2004 supplied less a mounting bracket.
- 7. CSC-2016; same as CSC-2010 supplied less a mounting bracket.
- 8. CSC-2018; 0 to 2" Δ P, 11.5 scim air consumption.

FLOW CHARACTERISTICS



FIELD ADJUSTMENTS (Cooling Application With A Reverse Acting Thermostat)

- 1. The controller must be firmly mounted in it's bracket on the terminal unit.
- 2. The controller must be piped as follows:
 - 1/4" O.D. tubing; "T" port to the thermostat branch signal.
 - 1/4" O.D. tubing; "M" port a clean and dry main air supply (15 to 30 psig).
 - 1/4" O.D. tubing; "B" port to the damper actuator.
 - 3/8" O.D. tubing; "Y" port to the total pressure on the ΔP pick-up (high).
 - 3/8" O.D. tubing; "X" port to the static pressure on the ΔP pick-up (low).
 Note: The controller does not bleed to atmosphere. The actuator exhaust from the "B" port and the main air exhaust are vented into the lower chamber and through the "Y" port. 3/8" tubing should be used for the "Y" port connections and the length should be kept to a maximum of 18" 24" to avoid unnecessary resistance.
 Otherwise hunting conditions can occur.
- 3. Use a flow hood, or "tee" a magnahelic between the controller and the ΔP pick-up.
- 4. The "HI" Limit must be set first. Temporarily adjust the thermostat for a branch pressure lower than the 3 psig reset start-point (maximum cooling), typically 1 psig or less is best. Removing the thermostat branch line would be another acceptable method. Adjust the "HI" knob (center knob) counterclockwise to increase or clockwise to decrease ΔP limit. Nominally one-half turn will net a 0.10" ΔP change. Allow for reaction time. Depending on actuator size and position, timing will vary. To position an actuator/damper from closed to open could require a couple minutes.
- 5. The "LO" Limit must be set after the "HI" Limit is set. Temporarily adjust the thermostat for a branch pressure higher than the 8 psig reset stop point (minimum cooling), typically 12 psig or greater is best. Removing the thermostat branch line and teeing in to the main air line would be another acceptable method. Adjust the "LO" knob (outside knob) counterclockwise to increase or clockwise to decrease ΔP limit. Nominally one-half turn will net a 0.10" ΔP change. Allow for reaction time.
- 6. Recheck the "HI" Limit and the "LO" Limit settings at least twice, verify settings and fine tune each time if necessary. This procedure will remove internal component tensions and confirm settings.
- 7. Adjust the thermostat to the desired room temperature setpoint. Be certain to reconnect the thermostat branch line if this method was utilized.

PRESSURE INDEPENDENT OPERATION

Differential pressure is sensed via a ΔP pick-up mounted up-stream of the damper (vav terminal inlet). The ΔP pick-up is a dual pressure pick-up sensing both Total Pressure and Static Pressure. The Total Pressure is connected to the "Y" port and the Static Pressure is connected to the "X" port. These two pressures are compared across the static diaphragm which takes a position relative to the difference of the two pressures, the force of the HI Limit adjustment spring in the upper chamber, and the force of the LO Limit adjustment spring in the lower chamber. Turning the "HI" knob counterclockwise (to increase) compresses the HI Limit adjustment spring placing a greater downward force on the diaphragm; increasing the pressure at the "B" port; increasing air through the vav terminal. Turning the "LO" knob adjustment spring counterclockwise positions the LO Limit stop downward limiting the travel of the piston cup; limiting the amount of reset; setting the minimum air flow through the vav terminal. When the "LO" knob is turned fully counterclockwise, the LO Limit will equal the HI Limit and the controller will function as a constant volume controller.

An increase in air flow is sensed via the increase in ΔP across the static diaphragm positioning the static diaphragm away from the nozzle decreasing the "B" port pressure to the actuator decreasing air flow until the static diaphragm comes into balance at the desired ΔP setpoint.

A decrease in air flow is sensed via the decrease in ΔP across the static diaphragm positioning the static diaphragm closer to the nozzle increasing the "B" port pressure to the actuator increasing air flow until the static diaphragm comes into balance at the desired ΔP setpoint.

RESET OPERATION

With sufficient air flow and a thermostat signal connected to the "T" port less than 3 psig, the controller will position the actuator to regulate air flow at the HI Limit setting. In this state the static diaphragm is balanced over the nozzle through the forces of the opposing springs and forces of the Total and Static Pressures. When the thermostat signal increases above 3 psig the piston cup will begin to position the reset lever upward increasing the force of the LO Limit spring positioning the static diaphragm away from the nozzle closing the damper for less air flow requiring a lower ΔP to re-balance the static diaphragm. The ΔP setpoint of the controller has been reset downwards with the increasing thermostat signal. The stroke of the piston cup is limited via the LO Limit knob. Raising the LO Limit will reduce the top end of the reset span narrowing the reset span. At each new ΔP setpoint, as dictated by the thermostat signal, the static diaphragm will again balance.



REVERSE ACTING RESET VOLUME CONTROLLER CSC-2000 SERIES (GRAY CONTROLLERS)

