

A reverse acting, two-pipe thermostat is required. Damper is normally open. Optional reheat control will require a normally closed hot water valve or a normally open P.E. switch. On a rise in space temperature airflow is increased. On a drop in space temperature airflow is decreased. Maximum and minimum CFM setpoints are field adjustable. Control of supply air to room is between these setpoints. If the space temperature continues to drop at minimum airflow, the thermostat will energize an optional electric heater or hot water coil valve to provide reheat. The controller can be calibrated to provide a constant reset range regardless of airflow limits.





CONTROLLER REQUIRES FIELD CALIBRATION AND SET UP
UNLESS OTHERWISE SPECIFIED. IF FACTORY CALIBRATION
OPTION IS USED, THE RESET SPAN AND STARTPOINT WILL
BE ADJUSTED AS SHOWN ABOVE UNLESS OTHERWISE SPECIFIED.

FACTORY PIPING ----FIELD PIPING

PNEUMATIC AIR CONSUMPTION 1.0 SCFH



TITLE:	SD410RC		[DATE:		DRAWING NO.
	PRESSURE INDEPENDENT PNEUMATIC CONTROLS	AWW		05/12/97		
	THIS DRAWING CONTAINS PROPRIETARY DATA. UNAUTHORIZED DISCLOSURE, REPRODUCTION, OR USE IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION		DATE: 08/1	19/08	REV: 02	17794

²HOT WATER VALVE SUPPLIED BY OTHERS P.E. SWITCH IS INCLUDED IN ELECTRIC HEATER

³UNIT SIZES 19 & 22 UTILIZE DUAL ROTARY PNEUMATIC DAMPER ACTUATORS.