

A reverse acting, two-pipe thermostat is required. Damper is normally closed. Optional reheat control will require a normally closed hot water valve or a normally open P.E. switch. With 18 PSIG main air pressure, normal variable volume control occurs. On a rise in space temperature airflow is increased. On a drop in space temperature airflow is decreased. Maximum and minimum CFM setpoints are field adjustable. Control of supply ait to room is between these setpoints. If the space temperature continues to drop at minimum airflow, the thermostat will energize an optional electric heater or hot these setpoints. If the space temperature continues to drop at minimum airflow, water coil valve to provide reheat. With 23 PSIG main air pressure, the damper modulates to the full open position to accomplish morning warm up. The controller can be calibrated to provide a constant reset range regardless of airflow limits.





CONTROLLER REQUIRES FIELD CALIBRATION
AND SET UP UNLESS OTHERWISE SPECIFIED.
IF FACTORY CALIBRATION OPTION IS USED, THE
RESET SPAN AND STARTPOINT WILL BE ADJUSTED
AS SHOWN ABOVE UNLESS OTHERWISE SPECIFIED.

² HOT WATER VALVE SUPPLIED BY OTHERS P.E. SWITCH IS INCLUDED IN ELECTRIC HEATER

——FACTORY PIPING ----FIELD PIPING

³ UNIT SIZES 19 & 22 UTILIZE DUAL ROTARY PNEUMATIC DAMPER ACTUATORS.

PNEUMATIC AIR CONSUMPTION 1.0 SCFH



TITLE:	SD413RC	DRN BY:	D.	ATE:		DRAWING NO.
	3D413RC	AWW		05/13/97		
	PRESSURE INDEPENDENT PNEUMATIC CONTROLS	^""				47707
		CKD BY:	DATE:		REV:	17797
	THIS DRAWING CONTAINS PROPRIETARY DATA. UNAUTHORIZED DISCLOSURE, REPRODUCTION, OR USE IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION	WAE	10/0	7/08	02	