

A reverse acting, two—pipe thermostat is required. Damper is normally open. Optional reheat control will require a normally closed hot water valve or or a normally open P.E. switch. With 18 PSIG main air pressure, normal variable volume control occurs. On a rise in space temperature, airflow is increased. On a drop in space temperature, airflow is decreased. Maximum and minimum CFM setpoints are field adjustable. Control of supply air to room is between these setpoints. If the space temperature continues to drop at minimum airflow, the thermostat will energize an optional electric heater or hot water coil valve to provide reheat. With 23 PSIG main air pressure, the damper modulates to the full open position to accomplish morning warm up.





-FACTORY PIPING ----FIELD PIPING

PNEUMATIC AIR CONSUMPTION 1.0 SCFH



TITLE:	SD414R			DATE: 05/09/97		16360	
PRESSU	RE INDEPENDENT PNEUMATIC CONTROLS	CKD BY: DATE: WAE 11/18					
THIS D	AWING CONTAINS PROPRIETARY DATA. UNAUTHORIZED DISCLOSURE,			18/08	REV:	10300	
REPRODU	REPRODUCTION, OR USE IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION		<u> L'''</u>	10/00	04		

CONTROLLER RESET RANGE
WILL VARY WITH AIRFLOW LIMITS

<sup>2</sup> HOT WATER VALVE SUPPLIED BY OTHERS P.E. SWITCH IS INCLUDED IN ELECTRIC HEATER

JUNIT SIZES 19 & 22 UTILIZE DUAL ROTARY PNEUMATIC DAMPER ACTUATORS