

A direct acting, two—pipe thermostat is required. Damper is normally open. Optional reheat control will require a normally open hot water valve or a normally closed P.E. switch. On a rise in space temperature, airflow is increased. On a drop in space temperature, airflow is decreased to minimum position. As space temperature continues to drop, the controller goes through a field adjustable dead band at minimum position and then increases to a higher field adjustable minimum for reheat. The cooling controller can be calibrated to provide a constant reset range regardless of airflow limits.





CONTROLLER REQUIRES FIELD CALIBRATION AND SET UP UNLESS OTHERWISE SPECIFIED. IF FACTORY CALIBRATION OPTION IS USED, THE RESET SPAN AND STARTPOINT WILL BE ADJUSTED AS SHOWN ABOVE UNLESS OTHERWISE SPECIFIED.

2 ADJUST FOR MAXIMUM AND MINIMUM COOLING SETPOINTS.

HEATING MINIMUM SETPOINT

HOT WATER VALVE SUPPLIED BY OTHERS

P.E. SWITCH IS INCLUDED IN ELECTRIC HEATER

<sup>5</sup> ADJUST DIVERTING RELAY TO DESIRED SWITCHOVER PRESSURE

ADJUST "LO" KNOB ONLY FOR

OUNIT SIZES 19 & 22 UTILIZE DUAL ROTARY PNEUMATIC DAMPER ACTUATORS

PNEUMATIC AIR CONSUMPTION 2.0 SCFH



P.E. SWITCH N.C.

TITLE:	SD428RC	DRN BY:		DATE: 05/13/97		DRAWING NO.
	PRESSURE INDEPENDENT PNEUMATIC CONTROLS	AWW				17806
		CKD BY:	DATE:		REV:	17000
	THIS DRAWING CONTAINS PROPRIETARY DATA. UNAUTHORIZED DISCLOSURE, REPRODUCTION, OR USE IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION	WAE	10/08/	/08/08 03		