

A reverse acting, two-pipe thermostat is required. Damper is normally closed. Reheat control requires a normally closed hot water valve or a normally open P.E. switch. As the space temperature decreases, cold airflow is decreased to minimum position. If the space temperature continues to drop, airflow is increased to maximum position and reheat is energized. Maximum and minimum CFM setpoints are field adjustable. The controller can be calibrated to provide a constant reset range regardless of airflow limits.





CONTROLLER REQUIRES FIELD CALIBRATION
AND SET UP UNLESS OTHERWISE SPECIFIED.
IF FACTORY CALIBRATION OPTION IS USED, THE
RESET SPAN AND STARTPOINT WILL BE ADJUSTED
AS SHOWN ABOVE UNLESS OTHERWISE SPECIFIED.

FACTORY PIPING ----FIELD PIPING

- HOT WATER VALVE SUPPLIED BY OTHERS P.E. SWITCH IS INCLUDED IN ELECTRIC HEATER
- UNIT SIZES 19 & 22 UTILIZE DUAL ROTARY PNEUMATIC DAMPER ACTUATORS

PNEUMATIC AIR CONSUMPTION 1.0 SCFH



TITLE:	SD433RC	DRN BY:		D	DATE:		DRAWING NO.
	5D453RC		AWW		05/14/97		47040
	PRESSURE INDEPENDENT PNEUMATIC CONTROLS						
		CKD BY:		DATE:		REV:	17812
	THIS DRAWING CONTAINS PROPRIETARY DATA. UNAUTHORIZED DISCLOSURE, REPRODUCTION, OR USE IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION	w	'AE	11/1	8/08	04	