
A reverse acting, two-pipe thermostat is required. Damper is normally open. Optional reheat control will require a normally closed hot water valve or a normally open P.E. switch. On a rise in space temperature, airflow is increased. On a drop in space temperature, airflow is decreased to minimum position. As space temperature continues to drop, the controller goes through a field adjustable dead band at minimum position and then increases to a higher field adjustable minimum for reheat. The cooling controller can be calibrated to provide a constant reset range regardless of airflow limits.



- 1 CONTROLLER REQUIRES FIELD CALIBRATION AND SET UP UNLESS OTHERWISE SPECIFIED. IF FACTORY CALIBRATION OPTION IS USED, THE RESET SPAN AND STARTPOINT WILL BE ADJUSTED AS SHOWN ABOVE UNLESS OTHERWISE SPECIFIED.
- 2 ADJUST FOR MAXIMUM AND MINIMUM COOLING SETPOINTS.

----FIELD PIPING ----FIELD PIPING

- 3 ADJUST "LO" KNOB ONLY FOR HEATING MINIMUM SETPOINT
- 4 HOT WATER VALVE SUPPLIED BY OTHERS P.E. SWITCH IS INCLUDED IN ELECTRIC HEATER
- 5 ADJUST DIVERTING RELAY TO DESIRED SWITCHOVER PRESSURE
- 6 UNIT SIZES 19 & 22 UTILIZE DUAL ROTARY PNEUMATIC DAMPER ACTUATORS

PNEUMATIC AIR CONSUMPTION 2.0 SCFH



| 7 | ITLE: SD430RC   | DRN BY:          |      | DATE:      |      | DRAWING NO. |
|---|---|------------------|------|------------|------|-------------|
| ı | 3D430NC   | l <sub>Aww</sub> |      | 05/1       | 3/97 |             |
|   | PRESSURE INDEPENDENT PNEUMATIC CONTROLS   | 7,1111           |      | 33, 13, 31 |      | 47000       |
| Н |   | CKD BY:          | DATE | :          | REV: | 17809       |
|   | THIS DRAWING CONTAINS PROPRIETARY DATA. UNAUTHORIZED DISCLOSURE, REPRODUCTION, OR USE IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION | WAE              | 10/  | 08/08      | 03   |             |