








This application provides single duct variable air volume cooling. As space temperature drops, airflow is reset from maximum to minimum setpoint. Air volume limits are located at the thermostat.



2" SQUARE LOW PROFILE ELECTRONIC THERMOSTAT



TO DIFFERENTIAL PRESSURE SENSOR

CONTROLLER ASSY. MODEL: ETPX0

- 1 MINIMUM 10 VA
- 2 WIRE TERMINAL 3 TO TERMINAL 1 IN THE FIELD
- 3 SEE ORDER ACKNOWLEDGEMENT FOR OPTIONAL ITEM REQUIREMENTS

--- FACTORY TUBING
 - - - - - FIELD WIRING
 _____ FACTORY WIRING

TITLE: **SD7000**
 PRESSURE INDEPENDENT ELECTRONIC CONTROLS



DRN BY: AWW	DATE: 05/12/97	SCALE: NA	DRAWING NO.
CKD BY: WAE	DATE: 04/09/08	REV: 11	19284

THIS DRAWING CONTAINS PROPRIETARY DATA. UNAUTHORIZED DISCLOSURE, REPRODUCTION, OR USE IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION

DO NOT SCALE DRAWING. DIMENSIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE. CONTACT FACTORY FOR CERTIFIED DRAWINGS.